


- R₁ 15000 OHMS
- R₂ 15000 "
- R₃ 10,000 "
- R₄ 120 "
- R₆ 15 "
- R₈ 200 "
- R₉ 750 "
- R₁₀ 259,000 Ω

Type and Position of Tubes		WITH DIAL AT 500 K.C.				DIAL AT 1500 K.C.									
		1st, 2nd, 3rd R.F. UY227		Det. UY227		1st A.F. UY227		2nd A.F. UX245		Rect. UX280		1st B.F. UY227		2nd B.F. UY227	
		On	Off	On	Off	On	Off	On	Off	On	Off	On	Off	On	Off
Plate volts.....	105	135	36-50	100	137	250	375	110-115	130-140	40-50	115	137	137	137	137
Grid volts.....	4.2	24-26	2.5-3.5	4.5	6.5	46	65	7-8	29	3-3.5	5-6	6-7	5.5	5.5	5.5
Plate m.a.....	5		.25	4	5.5	32		3.5		5	4.5	7	7	7	7
Plate current change (grid test)	10.5		.5	5.5	7	37		7.5		5	6	7	7	7	7
Filament volts....	2.3		2.3	2.3	2.3	2.3	4.9	2.3		2.3	2.3	2.3	2.3	2.3	2.3

Marconi Model 20



Marconi Model 20 Power Unit

